

FORMA

6940UFP150R05-28 GREY

EAN 4031582476316



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Forma
Housing type	Swivel castor
Load capacity at 3 km/h	135 kg
Temperature range (Minimum)	-18 °C
Temperature range (Maximum)	120 °C
Overall height	177 mm

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	18 mm
Hardness of tread (A)	60 Shore A

HOUSING

Material fork	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	57 mm
Swivel radius	137 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	40 mm

FORMA

6940UFP150R05-28 GREY

EAN 4031582476316



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

