PRODUCT INFORMATION

ICS

5328XSX125P51 7001 INOX 7001

EAN 4031582310344



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	ICS
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	166 mm
Overall width	52 mm
Overall weight	0.77 kg

HOUSING

Housing Material	Polyamide
Fork shape	Slim
Housing Color	Silver grey (similar RAL7001)
Dome diameter	52 mm

WHEEL

Body material	Polyamide, electric conductive
Tread Material Mix	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, sealed
Wheel Color	Silver grey (RAL7001)
Threadguards	Integrated threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	95 mm
Plate width	70 mm
Plate hole length (Maximum)	50 mm
Plate hole width (Maximum)	75 mm
Plate hole diameter	11 mm

IF Design Award

© Copyright 2026 TENTE International GmbH


ICS


5328XSX125P51 7001 INOX 7001


EAN 4031582310344

Order number 00030787

Product Drawings







IF Design Award

© Copyright 2026 TENTE International GmbH