

PRODUCT INFORMATION

MAXTECH

UAD125x40-Ø12 HL44,4

EAN 4031582452846



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Roller bearing, stainless |
| Diameter | 125 mm |
| Tread width | 40 mm |
| Axle Hole Diameter | 12 mm |
| Hub Length | 44.4 mm |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ○ ○ |
| Movement Noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product Name | Maxtech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 300 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 600 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.37 kg |

MAXTECH

UAD125x40-Ø12 HL44,4

EAN 4031582452846



BETTER MOBILITY. BETTER LIFE.

Product Drawings

