

STEM

S70-10x25 / 11 drilled stem

EAN 4031582411911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion Resistance	● ● ● ○ ○
----------------------	-----------

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Overall Height	6 mm
Overall weight	0.05 kg

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	25 mm