

LUMINA

6A23POI050B10-11X20/10 ZAMAK/9011

EAN 4031582311365



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor with intermittend brake
Standard	EN12529 - Swivel Chairs Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	59 mm
Overall width	55 mm
Overall weight	0.13 kg

HOUSING

Housing Material	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing, closed
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	20 mm
Swivel radius	54 mm
Swivel interference	108 mm
Dome diameter	0 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Graphite black (RAL9011)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

LUMINA

6A23POI050B10-11X20/10 ZAMAK/9011

EAN 4031582311365

Order number 00074986

Product Drawings



BETTER MOBILITY. BETTER LIFE.

