

LEVINA

5371PJP150R05-28X45

EAN 4031582363647



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Levina |
| Housing type | Swivel castor with directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 190 mm |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|----------------|
| Material fork | Polyamide |
| Fork shape | Slim |
| Swivel bearing | Two ball races |
| Offset | 38 mm |
| Swivel interference | 240 mm |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 28 mm |
| Bolt length | 45 mm |



Universal Design Award



Deutscher Designer Club

PRODUCT INFORMATION

LEVINA


5371PJP150R05-28X45

EAN 4031582363647



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Universal
Design
Award



Deutscher
Designer
Club