

PRODUCT INFORMATION

NOVATECH

ETP095x40-Ø20 HL45

EAN 4031582330403



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	881.85 lb
Electric conductive	no
Stainless	no
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	3.49 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.74 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	1.77 in
Hardness of tread (A)	92 Shore A
Bearing type	6204ZV

