

FOOTMASTER

FOOT MASTER GAGD-125-ASF-HUD

EAN 4031582495294



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	440 kg
Električni provod	no
nerdjajuci	no
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	175 mm
Ukupna širina	128 mm
Ukupna težina	10.68 kg

KUCISTE

ofset	33 mm
okretni radijus	100 mm
Otpor okretanju	200 mm
Prečnik kupole	130 mm

TOCAK

Nošenje	Nemašinsko glavcina
Prečnik	125 mm
Širina omotac	35 mm
Širina tela	35 mm

PRILAGOĐAVANJE

Dužina ploče	145 mm
Širina ploče	145 mm
Dužina otvora ploče (maksimalna)	120 mm
Širina otvora ploče (maksimalna)	120 mm
Prečnik otvora ploče	11 mm

FOOTMASTER

FOOT MASTER GAGD-125-ASF-HUD

EAN 4031582495294

Broj porudžbine 00800104
Product Drawings



BETTER MOBILITY. BETTER LIFE.

