

# NOVATECH

RK.ETP078X78-Ø47X16

EAN 4031582330069  
Order number 00832672



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.07 in
Tread width	3.07 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Ball bearing diameter	1.85 in
Ball bearing width	0.63 in

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1543.23 lb
Load capacity at 3.7 mph	1851.88 lb
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.49 lb

## TECHNICAL DRAWINGS

