PRODUCT INFORMATION

DURATECH

TOP 200x50-Ø25 HL60

EAN 4031582322736



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2645.54 lb
Load capacity at 3.7 mph	2204.62 lb
Electric conductive	no
Stainless	no
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	3.53 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6205

© Copyright 2026 TENTE International GmbH


DURATECH

TOP 200x50-Ø25 HL60

EAN 4031582322736

Order number 00802937

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

TOP 200x50-Ø25-HL60

EAN 4031582322736

Order number 00807137



© Copyright 2026 TENTE International GmbH