

ALPHA

3478URO100P62 TFR

EAN 4031582391596



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ○ ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	35 kg
Load capacity Static	70 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall weight	0.435 kg

WHEEL

Body material	Polyamide
Tread material	Wound tread made of canvas and phenolic resin
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	30 mm
Hardness of tread (A)	85 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Rectangular plate
Plate length	103 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	9 mm

ALPHA

3478URO100P62 TFR

EAN 4031582391596



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

Platte 3470-080P62-105x80

