PRODUCT INFORMATION

DURATECH

TOP 160x50-Ø20 HL60

EAN 4031582322705



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2248.71 lb
Load capacity at 3.7 mph	1873.93 lb
Electric conductive	no
Stainless	no
Load capacity Static	3747.85 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	2.36 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6204

© Copyright 2026 TENTE International GmbH


DURATECH

TOP 160x50-Ø20 HL60

EAN 4031582322705

Order number 00801134

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

TOP 160x50-Ø20 HL60

EAN 4031582322705

Order number 004001134



© Copyright 2026 TENTE International GmbH