

ELASTECH

IEP 300X55-Ø20 HL66

EAN 4031582319781

Broj porudžbine 00834703



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglicni lezaj
Boja TocaK	Crni mlaz (sličan RAL9005)
stitnici omotaca	Bez stražara
Prečnik	300 mm
Širina omotac	55 mm
dimenzija rupa osovine	20 mm
dužina glavnice	66 mm
Širina tela	55 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	480 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	3,892 kg

ELASTECH

IEP 300X55-Ø20 HL66

EAN 4031582319781
Broj porudžbine 00834703



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

