

ELASTECH

IEP 300X55-Ø20 HL66

EAN 4031582319781

Broj porudžbine 00834703



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

| | |
|----------------------------|-------------------------------------|
| Materijal za telo | Aluminijum |
| | mekan |
| materijal omotaca | Elastična guma, crna, vulkanizovana |
| Nošenje | precizini kuglični lezaj |
| Boja Tocak | Crni mlaz (sličan RAL9005) |
| stitnici omotaca | Bez stražara |
| Prečnik | 300 mm |
| Širina omotac | 55 mm |
| dimenzija rupa osovina | 20 mm |
| dužina glavčine | 66 mm |
| Širina tela | 55 mm |
| Teškoća gazećeg omotac (A) | 68 Šešelj A |

PERFORMANSE

Performanse kotrljanja ● ● ● ● ●

Buka u pokretu ● ● ● ● ●

Ishrana ● ● ● ● ●

otpornost na rdju ● ● ● ● ●

OSNOVNI ATRIBUTI

| | |
|--------------------------------|------------------------------|
| Naziv proizvoda | Elastech |
| Tip | Tocak |
| Standard | EN12532 - transportna oprema |
| Nosivost na 4 km/h | 600 kg |
| Nosivost na 6 km/h | 480 kg |
| Statički Nosivost | 1200 kg |
| Temperaturni opseg (Minimalno) | -20 °C |
| Opseg temperature (maksimalni) | 85 °C |
| Ukupna težina | 3,892 kg |

ELASTECH

IEP 300X55-Ø20 HL66

EAN 4031582319781
Broj porudžbine 00834703



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

