

PRODUCT INFORMATION

# PURETECH

PVO200x50-Ø20 HL58

EAN 4031582442373



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (A)	85 Shore A

## PERFORMANCE

Roll Performance	● ● ● ○ ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ○ ○ ○
Corrosion resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	451.95 lb
Electric conductive	no
Stainless	no
Load capacity Static	903.89 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	3.01 lb

# PURETECH

PVO200x50-Ø20 HL58

EAN 4031582442373



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

