

AGILA

2477PJO075P30-11

EAN 4031582050363



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Agila |
| Type | Swivel caster with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 165.35 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 330.69 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.94 in |
| Overall width | 1.69 in |
| Overall weight | 0.59 lb |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 0.94 in |
| Swivel radius | 3.15 in |
| Swivel interference | 6.3 in |
| Dome diameter | 1.69 in |

WHEEL

| | |
|-----------------------|-----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Body width | 0.98 in |
| Hardness of tread (A) | 87 Shore A |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA

2477PJO075P30-11

EAN 4031582050363

Order number 00003358
Product Drawings



BETTER MOBILITY. BETTER LIFE.

