

AGILA

2478PJI050P41-55

EAN 4031582030013
Order number 00003898



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.72 in
Overall width	1.38 in
Overall weight	0.19 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Color	Blue passivated
Dome diameter	1.06 in

FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	2.17 in
Plate hole length (Minimum)	1.52 in
Plate hole length (Maximum)	1.73 in
Plate hole width (Minimum)	1.52 in
Plate hole width (Maximum)	1.73 in
Plate hole diameter	0.25 in

AGILA

2478PJI050P41-55

EAN 4031582030013
Order number 00003898



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

