

ALPHA

3480PQR260P65 BLACK/DARKBLUE

EAN 4031582438239



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Load capacity at 3 km/h	150 kg
Load capacity Static	300 kg
Overall height	310 mm
Overall weight	5 kg

WHEEL

Body material	Polypropylene
Tread material	Pneumatic tyre, block profile
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	260 mm
Tread width	85 mm

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races, reinforced or stainless
Offset	90 mm
Swivel radius	220 mm
Swivel interference	440 mm

FITTING

Fitting type	Rectangular plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	14 mm

PRODUCT INFORMATION

ALPHA

3480PQR260P65 BLACK/DARKBLUE

EAN 4031582438239



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

