

PRODUCT INFORMATION

NOVATECH

ETP085x90-Ø17 HL90

EAN 4031582369465



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |          |
|-----------------------------|----------|
| Product Name                | Novatech |
| Type                        | Wheel    |
| Load capacity at 3 km/h     | 800 kg   |
| Electric Conductive         | No       |
| Stainless                   | No       |
| Load capacity Static        | 1600 kg  |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Steel, iron            |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 85 mm                  |
| Tread width           | 90 mm                  |
| Axle Hole Diameter    | 17 mm                  |
| Hub Length            | 90 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Bearing type          | 6303                   |

