

PRODUCT INFORMATION

DURATECH

TOP 082x91-Ø20 HL93

EAN 4031582322637



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1984.16 lb
Load capacity at 3.7 mph	1587.33 lb
Electric conductive	no
Stainless	no
Load capacity Static	3968.32 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.25 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.23 in
Tread width	3.58 in
Axle hole diameter	0.79 in
Hub length	3.66 in
Body width	3.58 in
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

DURATECH

TOP 082x91-Ø20 HL93

EAN 4031582322637

Order number 00804152
Product Drawings



BETTER MOBILITY. BETTER LIFE.

