

STEM

S70-10x35 / 11

EAN 4031582452723



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	35 mm

PERFORMANCE

Corrosion Resistance ●●●○○

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Overall Height	6 mm
Overall weight	0.04 kg