

BASETECH

POO065X30-Ø12

EAN 4031582418965



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	65 mm
Tread width	30 mm
Axle hole diameter	12 mm
Hub length	34.5 mm
Hardness of tread (D)	65 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	120 kg
Load capacity Static	240 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.047 kg

BASETECH

POO065X30-Ø12

EAN 4031582418965



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

