PRODUCT INFORMATION

SUPRATECH

PJP125x32-Ø8,3 2.0

EAN 4031582070

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle Hole Diameter	8 mm
Hub Length	36.5 mm
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Supratech
CO2 emission (scope 3)	0.99
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.24 kg

© Copyright 2026 TENTE International GmbH


SUPRATECH

PJP125x32-Ø8,3 2.0

EAN 4031582070

Order number 10010291

Product Drawings



© Copyright 2026 TENTE International GmbH