

ELASTECH

SFP 160x50-Ø20 HL60 plus

EAN 4031582322200



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Čelik od limova, težak
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Siva/ne-označavanje
stitnici omotaca	Sa threadguard
Prečnik	160 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	540 kg
Nosivost na 6 km/h	450 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	900 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	1.12 kg

ELASTECH


SFP 160x50-Ø20 HL60 plus

EAN 4031582322200

Broj porudžbine 00830558
Product Drawings



BETTER MOBILITY. BETTER LIFE.




ELASTECH

SFP 160x50-Ø40 HL60 plus

EAN 4031582322700

Broj porudžbine 0084558



BETTER MOBILITY. BETTER LIFE.