

STEM

B40 - 11X20 / 10

EAN 4031582418002



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Overall height	4.5 mm
Overall weight	0.035 kg

FITTING

Fitting type	Stem with synthetic circlip, with collar
Stem diameter	11 mm