

DURATECH HEAT

WOG 075X25 HL27 BLACK

EAN 4031582382884
Order number 00039930



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	134 °C
Overall weight	0.084 kg

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Black
Diameter	75 mm
Tread width	25 mm
Axle hole diameter	8 mm
Hub length	27 mm
Body width	25 mm
Hardness of tread (D)	80 Shore D

HOUSING

Stainless	✓
-----------	---

DURATECH HEAT

WOG 075X25 HL27 BLACK

EAN 4031582382884
Order number 00039930



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

