

# ALPHA STAINLESS

8477UAD100P30-11 RED

EAN 4031582370164



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	330.69 lb
Stainless	✓
Load capacity Static	661.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	5.04 in
Overall weight	2.11 lb

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (D)	42 Shore D

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel interference	9.53 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

# ALPHA STAINLESS

8477UAD100P30-11 RED

EAN 4031582370164



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

