

# NOVATECH

ITP 100X40-Ø15 HL40

EAN 4031582324525  
Order number 00830926



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle hole diameter	15 mm
Hub length	40 mm
Body width	40 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.576 kg

# NOVATECH

ITP 100X40-Ø15 HL40

EAN 4031582324525  
Order number 00830926



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

