

SUPRATECH

PJP5X1.25-Ø9.8 HL41

EAN 4031582436150



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	127 mm
Tread width	31.75 mm
Axle hole diameter	9.8 mm
Hub length	41 mm
Hardness of tread (A)	77 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	125 kg
Load capacity Static	250 kg

SUPRATECH

PJP5X1.25-Ø9.8 HL41

EAN 4031582436150



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

