

OMIKRON

9250STP250P65

EAN 4031582314038
Order number 00830227



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	5820.2 lb
Load capacity at 3.7 mph	4850.16 lb
Load capacity Static	11640.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.8 in
Overall weight	74.13 lb

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.94 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Straight
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	2.95 in
Swivel radius	7.87 in
Swivel interference	15.75 in

FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	6.3 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.59 in

TECHNICAL DRAWINGS

