

MAXTECH

PNP 200X30-Ø8 HL60

EAN 4031582320633
Order number 00005569



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
	soft
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Wheel color	Black
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.18 in
Axle hole diameter	0.31 in
Hub length	2.36 in
Body width	1.18 in
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.88 lb

MAXTECH

PNP 200X30-Ø8 HL60

EAN 4031582320633
Order number 00005569



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

