

# PURETECH

PIR 125X37-Ø12 HL48

EAN 4031582320350  
Order number 00030824



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Axle hole diameter	12 mm
Hub length	48 mm
Body width	37 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.473 kg

PRODUCT INFORMATION

# PURETECH

PIR 125X37-Ø12 HL48

EAN 4031582320350  
Order number 00030824



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

