

ELASTECH

IFP160X50-Ø20

EAN 4031582319811

Broj porudžbine 00805136



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglični lezaj
stitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	350 kg
Nosivost na 6 km/h	280 kg
Statički Nosivost	700 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	1,204 kg

ELASTECH

IFP160X50-Ø20

EAN 4031582319811
Broj porudžbine 00805136



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

