

# ALPHA STAINLESS

8470UAD100P30-11 RED

EAN 4031582370072



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall weight	0.801 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	100 mm
Tread width	32 mm
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	91 mm
Swivel interference	182 mm
Stainless	✓

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# ALPHA STAINLESS

8470UAD100P30-11 RED

EAN 4031582370072



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

