

DURATECH

UOP200X50-Ø20

EAN 4031582323528
Broj porudžbine 00002304

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	20,1 mm
dužina glavcine	60 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	800 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,006 kg

DURATECH

UOP200X50-Ø20

EAN 4031582323528
Broj porudžbine 00002304



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

