

AGILA

2470PJI050B10-11X31 SCREWED

EAN 4031582300710
Order number 00004473



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	72 mm
Overall width	43 mm
Overall weight	0.172 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm
Dome diameter	41 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	31 mm

AGILA

2470PJ050B10-11X31 SCREWED

EAN 4031582300710
Order number 00004473



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

