

# NOVATECH

ETY 100X20-Ø20 HL14

EAN 4031582318845  
Broj porudžbine 00830221

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj (RS/2RS)
Boja Tocak	Med žuta (RAL1005)
Prečnik	100 mm
Širina omotac	20 mm
dimenzija rupa osovina	20 mm
dužina glavčine	14 mm
Širina tela	20 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	180 kg
Nosivost na 6 km/h	140 kg
Statički Nosivost	360 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,4 kg

# NOVATECH

ETY 100X20-Ø20 HL14

EAN 4031582318845  
Broj porudžbine 00830221



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

