

PRODUCT INFORMATION

MAXTECH

PNR400x90-Ø20 HL74 TBL

EAN 4031582411058



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	145 kg
Electric Conductive	No
Stainless	No
Load capacity Static	290 kg
Overall weight	3 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	90 mm
Axle Hole Diameter	20 mm
Hub Length	74 mm

