PRODUCT INFORMATION

# DURATECH

## MOP 200x50-Ø35 HL60

EAN 4031582320053



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Polyamide, super heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 7.87 in |
| Tread width | 1.97 in |
| Axle hole diameter | 1.38 in |
| Hub length | 2.36 in |
| Body width | 1.97 in |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6307 |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement noise | ●●○○○ |
| Attrition | ●●●●● |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Duratech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 7407.52 lb |
| Load capacity at 3.7 mph | 6172.94 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 12345.87 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 5.68 lb |

© Copyright 2026 TENTE International GmbH


# DURATECH

## MOP 200x50-Ø35 HL60

EAN 4031582320053

Order number 00801262

**Product Drawings**





© Copyright 2026 TENTE International GmbH

# DURATECH

## MOP 200x50-Ø35 HL60

EAN 4031582320053

Order number 00801262




BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH