

ALPHA STAINLESS

8478UOO160P63

EAN 4031582313413
Order number 00035545



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Housing type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 1102.31 lb |
| Load capacity Static | 2204.62 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 7.87 in |
| Overall width | 4.53 in |
| Overall weight | 3.14 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 6.3 in |
| Tread width | 1.57 in |
| Body width | 1.57 in |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|------------|------------------------|
| Material | Stainless steel, heavy |
| Fork shape | Broad |
| Color | Stainless steel |
| Stainless | ✓ |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 5.39 in |
| Plate width | 4.53 in |
| Plate hole length (Minimum) | 2.95 in |
| Plate hole length (Maximum) | 3.15 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 4.13 in |
| Plate hole diameter | 0.43 in |

ALPHA STAINLESS

8478UOO160P63

EAN 4031582313413
Order number 00035545



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

