

AGILA

2470UAP125R07-Ø31-35

EAN 4031582325690



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	163 mm

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel radius	103.5 mm
Swivel interference	207 mm

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	31 mm
Expander fitting (Maximum)	35 mm
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470UAP125R07-Ø31-35

EAN 4031582325690



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

