

COMPACTA

1530PJO050P41

EAN 4031582428407



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Compacta |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 50.71 lb |
| Load capacity Static | 101.41 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 2.36 in |
| Overall weight | 0.19 lb |

WHEEL

| | |
|-----------------------|----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 1.97 in |
| Tread width | 0.91 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---------------------------------------|
| Material | Steel sheet, light |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel bearing | One ball race |
| Offset | 0.87 in |
| Swivel radius | 1.85 in |
| Swivel interference | 3.7 in |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 1.46 in |
| Plate width | 1.46 in |
| Plate hole length (Maximum) | 1.18 in |
| Plate hole width (Maximum) | 1.18 in |