

# STYLEA

5920UOI055L51-8

EAN 4031582406382



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	57 mm
Overall width	37 mm
Overall weight	0.65 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	55 mm
Tread width	11 mm

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	47 mm
Swivel interference	94 mm
Dome diameter	18 mm

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	8 mm

# STYLEA

5920UOI055L51-8

EAN 4031582406382



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

