

NOVATECH

ITP 250x55-Ø20 HL66

EAN 4031582070347



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	55 mm
dimenzija rupa osovina	20 mm
dužina glavnice	66 mm
Širina tela	55 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	1000 kg
Nosivost na 6 km/h	800 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	2000 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2.34 kg




NOVATECH

ITP 250x55-020 H166

EAN 403158207054

Broj porudžbine 00834555



BETTER MOBILITY. BETTER LIFE.