

STYLEA

5920UJI065L51-11 DOM23X43,6 ALU

EAN 4031582335910



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Stylea |
| Housing type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 50 kg |
| Load capacity Static | 100 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 91.5 mm |
| Overall width | 46 mm |

WHEEL

| | |
|----------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 65 mm |
| Tread width | 7 mm |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 53 mm |
| Swivel interference | 106 mm |
| Dome diameter | 23 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 11 mm |

PRODUCT INFORMATION

STYLEA

5920UJI065L51-11 DOM23X43,6 ALU

EAN 4031582335910



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

