

MONO

5025PJH080S70-10X15 TFR

EAN 4031582385762



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Mono
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	110 mm
Overall weight	0.199 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	34 mm
Swivel radius	74 mm
Swivel interference	148 mm
Thread diameter	0 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm

MONO

5025PJH080S70-10X15 TFR

EAN 4031582385762



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

