

# ALPHA

3478POJ108P62 T/G-small

EAN 4031582306613



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Alpha                         |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 150 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 300 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall Height              | 132 mm                        |
| Overall width               | 85 mm                         |
| Overall weight              | 0.41 kg                       |

## HOUSING

|                  |                    |
|------------------|--------------------|
| Housing Material | Steel sheet, heavy |
| Fork shape       | Broad              |
| Housing Color    | Blue passivated    |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread Material Mix    | Identical with wheel body |
| Bearing               | Roller bearing            |
| Axle                  | Screwed with nut          |
| Wheel Color           | Graphite black (RAL9011)  |
| Threadguards          | With threadguard          |
| Diameter              | 108 mm                    |
| Tread width           | 36 mm                     |
| Body width            | 36 mm                     |
| Hardness of tread (D) | 65 Shore D                |

## FITTING

|                             |                         |
|-----------------------------|-------------------------|
| Fitting type                | Small rectangular plate |
| Plate length                | 103 mm                  |
| Plate width                 | 85 mm                   |
| Plate hole length (Minimum) | 77 mm                   |
| Plate hole length (Maximum) | 60 mm                   |
| Plate hole width (Minimum)  | 77 mm                   |
| Plate hole width (Maximum)  | 80 mm                   |
| Plate hole diameter         | 9 mm                    |

# ALPHA

3478POJ108P62 T/G-small

EAN 4031582306613

Order number 00000936

Product Drawings



BETTER MOBILITY. BETTER LIFE.

