

PRODUCT INFORMATION

NOVATECH

ITP 100x40-Ø15 HL40 cv

EAN 4031582383867



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE


Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	529.11 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.01 lb

WHEEL

Tread profile	convex
Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.57 in
Axle hole diameter	0.59 in
Hub length	1.57 in
Body width	1.57 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Suitable for	pimespo_still_wagner




PRODUCT INFORMATION

NOVATECH

ITP 100x40-015 HL40 cv

EAN 4031582383967

Order number 00830212



BETTER MOBILITY. BETTER LIFE.