

ELASTECH HEAT

IDG100X35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Elastech heat
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Electric conductive	✓
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall weight	0.354 kg

WHEEL

Body material	Aluminium
Tread material	Damping, heat resistant
Bearing	Dry bearing bush
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (A)	75 Shore A

ELASTECH HEAT

IDG100X35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

