

DURATECH

TOP 082x70-Ø20 HL70

EAN 4031582322590



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	82 mm
Tread width	70 mm
Axle Hole Diameter	20 mm
Hub Length	70 mm
Body width	70 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1500 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.46 kg

DURATECH

TOP 082x70-Ø20 HL70

EAN 4031582322590

Order number 00805242
Product Drawings



BETTER MOBILITY. BETTER LIFE.

